



Spacer length is made to suit chamber port length..
 50mm is given as an example for a chamber port length
 of 210mm (210=100+160-50)

| ASSTV | ENG. | DRN. | DATE | SCALE |
|--|----------------------------|-----------------|--|--------------------|
| | | | | |
| MATERIAL | | FINISH | Tolerance Unless Otherwise Stated | |
| | | DEBURR & POLISH | Angular ± 15' | 0 ± 0.5 |
| | | | Surface Finish | 0.0 ± 0.2 |
| | | | ISO Coarse Threads, BS3643 Class 6H/6g | 0.00 ± 0.1 |
| PSP Vacuum Technology | | | | |
| Unit 8,Heather Close,Lyme Green Business Park, Macclesfield,Cheshire,SK11 0LR. Tel:01625 500154 | | | | |
| TITLE | ISIS3000 Ion Source | | | DRAWING No. |